







Coil is happy to present our new hand held LED illuminated magnifier ATmax.

In the new ATmax product we have combined the latest LED technology which is brighter and more efficient. The specially designed diffuser gives an even and balanced spread of light across the lens.

The bi-aspheric lenses have been designed with a larger field of view, improved acuity with less peripheral distortion.

The automatic touch technology allows you to turn the LED light on by simply by holding the product. To turn the magnifier off you just put the magnifier down. There are no difficult switches.

The new LED range includes 5x and 7x circular lenses and for the first time Coil have designed a 3x rectangular lens. All magnifiers are supplied with a soft pouch to protect them when they are not being used.

Features

- Larger field of view
- Improved illumination
- Latest LED technology
- Coil Quality Lenses
- Touch control on/off
- · Ergonomic styling
- Lightweight
- · Battery push side switch
- · Soft cloth pouch

Benefits

- Offers a significantly larger viewing area
- Uniform spread of light across the entire lens
- Provides higher brightness, longer lasting life
- · Low distortion levels, improved acuity
- Ease of use for patients with poor dexterity
- Sits comfortably in the natural shape of hand
- Comfortable to hold for longer periods
- Enables easy access to change AA batteries
- Pouch protects magnifier whilst not in use

Technical Specifications

	Magnification	Effective Power	Effective Focal length (mm)	Lens Type	Lens Dimension (mm)
8273	3.0X	9D	111.54	Bi-aspheric	83x59
8275	5.0X	16D	62.5	Aspheric	<i>⁄</i> 260
8277	7.0X	24D	42.37	Aspheric	<i>⊘</i> 57.6

8201ATM (Display case)



UK Address:

Coil UK (Wipac Ltd) London Road, Buckingham MK18 1BH United Kingdom

Tel: +44 (0)1280 825942 Fax: +44 (0)1280 822802

US Address:

Coil USA (CTP Inc) 600, Depot Street Latrobe PA 15650 USA

Office No: 724-539-6991 Fax No: 724-537-2534